

# Usage of customer-owned tracking devices onboard of Lufthansa Cargo and Lufthansa Group Airlines flights

#### General

Lufthansa Cargo and the airlines of the Lufthansa Group, Lufthansa, Austrian Airlines, Swiss and Brussels Airlines, allow the usage of certain customer-owned cargo tracking devices being sent along with their shipments on our global network. Please note that if a device has been approved by Lufthansa this approval is valid for all Lufthansa as well as Lufthansa Cargo flights and also for all SN Brussles, Sun Express and Air Dolomiti flights.

Cargo tracking devices are personal electronic devices (PED) attached to or transported in airfreight with the purpose of monitoring location and/or various parameters, such as temperature, vibration, humidity. The device may transmit these parameters remotely by means of radio frequency emissions. Devices that do not actively transmit data are defined as "loggers" and subject to the same regulations.

As all of these devices remain switched on during flight, a technical evaluation by the operator is required. Data transmission must be suspended and disabled during flight in order to comply to air safety regulations.

#### Contact

Our customers are obliged to inform us about their intent of using customer-owned cargo tracking devices being sent along with their shipment. You can do this by simply activating the tick box "Realtime tracking" during the online booking process.

Should you have any questions regarding the requirements on how to book a cargo tracking device with your Lufthansa Cargo or Lufthansa Group airlines shipment, please contact your respective local sales representative.

For technical questions about the devices, please contact the respective manufacturer.

If you are interested in approvals for tracking devices other than listed here please contact your local sales representative.



#### Guideline

The following listed devices are accepted to be used aboard our airlines as depicted. The devices are not approved for transportation on interline routings with other carriers. Lufthansa Cargo and Lufthansa Group airlines will not be responsible for damages or losses of any tracking device in transit.

Lufthansa Cargo and Lufthansa Group airlines are constantly assessing new cargo tracking devices for usage aboard their aircraft and will update its list of approved devices here.

Concessions to use the listed devices are based upon current provisions and can be revoked at any time.

### Kindly observe following general guidelines concerning your cargo tracking devices:

- Tracking devices have to be maintained in a good and safe condition in order to avoid a modification to its emission characterization and to avoid a fire hazard through its batteries
- Consider IATA guidelines "Battery powered Tracker"
- New devices can only be approved prior to technical assessment of Lufthansa Cargo and Lufthansa Group airlines
- Hard- and software changes on already approved devices have to be reported to local sales representative to allow reevaluation of device.
- All devices must be securely enclosed within the shipment





(	<ul><li>Lufthansa</li></ul>	Austrian 🖊	<b>A</b> swiss	brussels airlines
Cargo Tracking Device Manufacturer I Designation	<b>Approved</b> Lufthansa Cargo	<b>Approved</b> Austrian Airlines	<b>Approved</b> Swiss Airlines	Approved Brussels Airlines
<b>7P Solutions</b> GD 100, GL 200 <sup>2</sup> , GL 300, GL 300W	<b>√</b> 1	* 1	<b>√</b> ²	$\checkmark$
Adapt Ideations Kelvin & Track IT	✓	*	✓	<b>√</b>
<b>Aspion</b> G-Log, G-Log waterproof	<b>√</b>	✓	<b>√</b>	<b>√</b>
BeOn A1	<b>√</b>	<b>√</b>	<b>√</b>	<b>√</b>
<b>Berlinger</b> SmartMonitor Ship M SmartMonitor Ship L	<b>√</b>	* *	<b>✓</b>	<b>*</b>
<b>Bosch</b> Basic Sense Type S, Type T, Basic Sense I <sup>3</sup> , TDL140 <sup>3,5</sup> ,TDL110 <sup>4</sup>	<b>√</b> 3	<b>√</b> <sup>4</sup>	5	<b>✓</b>
<b>CalAmp*</b> SC1004**,SC1204 <sup>6</sup> , SC1102**SC1204 <sup>6</sup> , SC1204 <sup>6</sup> , SC1100 <sup>7</sup> , STAG04HT SC1302	✓ <sup>6</sup>	<b>√</b> * 7,8	** 6,7	<b>×</b>
Cargosense Toshiba Environmental Logger	<b>√</b>	×	<b>√</b>	<b>√</b>
CartaSense U-Sensor	<b>√</b>	<b>√</b>	<b>√</b>	<b>√</b>
Controlant CO 10.01, Saga**, Saga H <sup>9</sup> , Saga P <sup>9</sup>	<b>✓</b>	*	** 9	<b>√</b>
DHL Smart Sensor RFID	<b>√</b>	×	*	<b>√</b>
<b>DeltaTrack Inc.</b> FlashLink Dry Ice USB PDF In-Transit Logger (Models of 407xx series)	✓			<b>√</b>
ECS GWS-CSCG Logistic Monitoring Gateway	$\checkmark$	<b>✓</b> *	*	$\checkmark$
ELPRO LIBERO CB, CD, CE, CH, CI, CL, CS LIBERO GE, GF, GH, GL, GS	<b>*</b>	<b>*</b>	** **	<b>*</b>
Emerson Electric Co. GO Real-Time 4G/5G, XL 4G/5G, 4G/5G Reusable EMERSON GO Real-Time 4G/5G Global EMERSON GO Real-Time 4G/5G Global Plus	<b>*</b>	<b>√</b> ∗	✓	<b>* * * * * * * * * *</b>

<sup>\*</sup> Device only approved on Austrian Airline flights for COVID-19-Shipments upon request. Please contact cargomanager@austrian.com for individual approval. (Devices >100mW are not permitted on OS B767 fleet operated flights, a case-by-case assessment is therefore required to ensure requested route will not be operated with OS B767 \*\* Kindly refer to https://www.swissworldcargo.com/en/activetrackingdevices for further important information
For 7P Solutions devices, following settings have to be ensured before usage on board: Flight Mode (OnOff enable) = Activated, GPS fix available (OnTline) > 5min, GPS fix unavailable (OffTime) < 1min, Minimum TX Altitude (SFAIt) <2000m, Maximum TX Speed (SFSpeed) <100 km/h
27 PS olutions GL 200 not permitted to be used aboard of Swiss flights
3 Bosch Basic Sense I, TDL140 not permitted to be used aboard of Austrian Airlines flights
5 Only Bosch TD 140 permitted to be used aboard of Swiss flights
6 CalAmp SC1204 not permitted to be used aboard of Lufthansa and Lufthansa Cargo flights and Swiss flights
7 CalAmp SC1100 not permitted to be used aboard of Austrian Airlines flights and Swiss flights | 8 CalAmp sC1102, SC1994, 1204 not permitted on O S 767 aircrafts | 9 000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted to be used aboard of Swiss flights | 1000 permitted permitted to be used aboard of Swiss flights | 1000 permitted permitted to be used aboard of Swiss flights | 1000 permitted permitted permitted permitted permitted permitted permitted permitted

## **Lufthansa Cargo** Networking the world.

	Lufthansa	Austrian 🖊	<b>SWISS</b>	brussels airlines
Cargo Tracking Device Manufacturer   Designation	<b>Approved</b> Lufthansa Cargo	Approved Austrian Airlines	Approved Swiss Airlines	Approved Brussels Airlines
<b>GEGO</b> Global Tracker V1, V1W	<b>√</b>	×	×	<b>√</b>
Freight Logger FreightLogger Mk1	<b>√</b>			✓
<b>Frigga</b> Frigga V5 series	✓			✓
<b>GEO</b> Single Use IoSC Edge (V2)	✓	*	*	✓
<b>Hanhaa</b> ParceLive	<b>√</b>	*	<b>√</b>	<b>√</b>
<b>HERE Technologies</b> HERE Premier Tracker	<b>√</b>		<b>√</b>	<b>√</b>
Hive-Zox Beecon, BEEconloT <sup>9</sup> BEEconloT with Probe BEEconloT	<b>\frac{1}{2}</b>	×	<b>√</b> 9	<b>✓</b>
Honeywell RTHAL-C1, 3G- ST-THALP-1, BluTag 360 <sup>10</sup>	0	10	**	<b>√</b>
Intelyt iCHIME, iTAG	<b>√</b>	<b>√</b>	✓	<b>√</b>
iTraq iTraq Butterfly	✓	*	•	<b>✓</b>
Kirsen Global Security Schenker Smartbox A-Type	<b>✓</b>	*	<b>✓</b>	<b>√</b>
<b>Logmore</b> TAG Sensor	<b>✓</b>	·	·	✓
LogTag Recorders Ltd. LogTag TRIX-8 LogTag TRIX-16	<b>*</b>			<b>✓</b>
<b>Modum</b> MODsense T	<b>√</b>	<b>√</b>	<b>✓</b>	✓
Moog Sense Aware 3000, ILC 3000	<b>√</b>	*	<b>√</b>	✓
Murata Manufacturing Co.,Ltd. muRata LBBC0ZZ2AM-690		$\checkmark$		
MSR Electronics MSR 63, 64, 83, 84 MSR 145, 165, 175 MSR 145B4, 145B7,145B8, MSR145B15, 145B16, MSR165B8 MSR165 B52 MSR175B16T2AA5, MSR175B16T6H3P5AA5L2 MSR175plus, 175B56T6H3P5AA5L2G	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	×	11	×

<sup>\*</sup> Device only approved on Austrian Airline flights for COVID-19-Shipments upon request. Please contact cargomanager@austrian.com for individual approval. (Devices >100mW are not permitted on OS B767 fleet operated flights, a case-by-case assessment is therefore required to ensure requested route will not be operated with OS B767) **Lufthansa Cargo**  $^{**} \ \text{Kindly refer to } \underline{\text{https://www.swissworldcargo.com/en/active}} \ \text{for further important information}$ Networking the world.

6	<b>Lufthansa</b>	Austrian 🖊	<b>SWISS</b>	brussels airlines
Cargo Tracking Device Manufacturer   Designation	Approved Lufthansa Cargo	Approved Austrian Airlines	<b>Approved</b> Swiss Airlines	Approved Brussels Airlines
<b>OnAsset</b> Sentinel 100, 100 A, 100 B, 100 L, 100 P, 100 Sentry 500*,11 Sentry 600 Flight Safe	) S, 🗸	✓ * ✓	✓	✓ ✓
Onset Computer Corporation InTemp CX 501, CX 502, CX 503 InTemp CX 602, CX603, CX 702, CX 703	<b>✓</b>	<b>√</b> *	<b>√</b>	<b>√</b>
Roambee** BeeBeacon BeeSense Modbus Bee Air <sup>12</sup> Beacon Plus <sup>12</sup>	12	<b>√</b> .	13**	12 12
Plus Probe VOC <sup>12</sup> BeeSense Flex BeeSense	12	<b>*</b> ;	<b>*</b>	12
SAS Stracker STRACKER PT35	$\checkmark$	<b>√</b> *	$\checkmark$	$\checkmark$
Sendum PT300D	<b>✓</b>	*	<b>√</b>	<b>√</b>
SenseAware SA3000, PT300D* SenseAware 4000, M4, SenseAware ID, FedEx SenseAwareID	<b>√</b>	*	<b>√</b>	✓
Sensire TSN Pro	<b>√</b>	<b>✓</b> *	×	<b>√</b>
Sensitech TempTale Geo Ultra / VizComm View Ultra (T11013050)	<b>✓</b>	<b>√</b> *	<b>√</b>	<b>√</b>
TempTale Geo Ultra Dry Ice (T11013070)	$\checkmark$	*	$\checkmark$	$\checkmark$
TempTale Geo Ultra Extended / VizComm View Ultra Extended (T11012990), Li Battery	*	×	×	*
TempTale GEO Ultra Dry Ice Extended (T11013060), Li Battery	×	×	×	*
TempTale ULTRA 16K AMBIENT	$\checkmark$			$\checkmark$
TempTale Ultra 16K (TempTale Ultra In-Transit Temperature Recorder / TempTale Ultra, 64K, Dry Ice Probe, Probe, Humidity, Ultra BIO		✓		✓
TempTale Ultra Multi-Use T11012940 T11012800 TT Ultra Dry Ice Ambient	<b>\frac{1}{2}</b>			<b>\( \)</b>
Shipit.to SIT1002	<b>√</b>	<b>✓</b> *	✓	<b>√</b>
SkyCell Savy Sensor (Model 800) SECURE Live MR Logger (810, 811, 812)	<b>\( </b>	<b>√</b>	<b>√</b>	<b>*</b>

<sup>\*</sup> Device only approved on Austrian Airline flights for COVID-19-Shipments upon request. Please contact cargomanager@austrian.com for individual approval. (Devices >100mW are not permitted on OS B767 fleet operated flights, a case-by-case assessment is therefore required to ensure requested route will not be operated with OS B767)



<sup>12</sup> Bee Air, Beacon Plus, Plus Probe VOC not permitted to be used aboard of Lufthansa and Lufthansa Cargo flights









Cargo Tracking Device Manufacturer   Designation	Approved Lufthansa Cargo	<b>Approved</b> Austrian Airlines	Approved Swiss Airlines	Approved Brussels Airlines
<b>Sony</b> Visilion Mobiam Tracker Visilion Tracker G100 (VT-G100)	<b>√</b>	<b>√</b> *	✓	Ý.
STEFANELLI ENTERPRISES Temp-Tock D Temp-Tock A	✓			<b>√</b>
System Loco Loco Tag E4BL HGR4 HGD4	<b>*</b>	✓ ✓ *		<del>*</del>
<b>Tag-n-Trac</b> Tag-n-Trac SLB1	✓	✓		✓
Tec4Med SmartBeacon TempBeacon CryoBeacon Smarthub / Smartlock	<b>*</b>	<b>∀</b> ,	<del>*</del>	<b>*</b>
Tempmate GmbH tempmate S1 V2 tempmate-S2 tempmate-GS2	<b>×</b>	✓	✓	✓ ✓ ×
<b>TempSen</b> ITAG3 Pro <sup>14</sup> , ITAG4, Bio, TH, SP, Tempod 30, 50X, 90S, 100X, 200X, 20B, 50XB, 100XB, 200XB, Alpha TH30	<b>√</b> 14	✓	×	✓
<b>Tive</b> TT-4000 (Flagship) TT-7000 (Solo 5G) TT-7100 (Non-Lithium)	<b>✓ ✓</b>	*	✓ ✓	<b>*</b>
<b>ToolLive</b> TL001	<b>✓</b>	<b>✓</b>	<b>✓</b>	<b>✓</b>
Trackonomy FBB-2000 FWB-2000	<b>✓</b>	<b>√</b> *	<b>√</b>	<b>√</b>
TSS TempTracer 2, 3, Humidity, BLE, WebLogger, II, Dry Ice	<b>✓</b>	<b>√</b>	<b>✓</b>	<b>→</b>
<b>T-Systems ECD</b> ECD Solid II	$\checkmark$	<b>√</b>	*	<b>√</b>
<b>Versa</b> Versa 1	$\checkmark$	*	<b>✓</b>	$\checkmark$
<b>zLogg LLC</b> Z1 Series (e.g. z1LcdMu, Z1H)	<b>✓</b>			<b>✓</b>

<sup>\*</sup> Device only approved on Austrian Airline flights for COVID-19-Shipments upon request. Please contact cargomanager@austrian.com for individual approval. (Devices > 100mW are not permitted on OS B767 fleet operated flights, a case-by-case assessment is therefore required to ensure requested route will not be operated with OS B767)



